








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.06.27	
A2	N/A	A2 X1		2025.08.23	



- Specifications()
- 1.Voltage rating():DC 30V
 - 2.Current rating():0.5A AC/DC
 - 3.Withstanding voltage():≥ 500V AC/minute
 - 4.Insulation resistance():≥ 100MΩ Min
 - 5.Contact resistance():≤ 30mΩ Max
 - 6.Mating cycles 5000 cycles Min
 - 7.Insertion and extraction force 3~20N
 - 8.Temperature range():-30 ~+70



7	Terminal 6	Phosphor Bronze=0.20mm	Ag
6	Terminal 5	Phosphor Bronze=0.20mm	Ag
5	Terminal 4	Phosphor Bronze=0.20mm	Ag
4	Terminal 3	Phosphor Bronze=0.20mm	Ag
3	Terminal 2	Phosphor Bronze=0.20mm	Ag
2	Terminal 1	Phosphor Bronze=0.20mm	Ag
1	Plastic	PA9T	Black
NO	PAPT NAMF	MATERIAL	PLATING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 3.5 PHONE JACK
CHECKED		UNIT: mm/in	PART NO.: PJ-342EX-SMT
APPROVED		SIZE: A4	DWG NO.: