





Kinghelm®



SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω , Min
Contact Resistance: 20m Ω , Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

RECOMMEND P.C.B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

深圳市金航标电子有限公司

www.kinghelm.com

KH-2.0DC3-2X5P-H5.7

0755-28190160

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ± 0.30 X° : $\pm 5^\circ$
X.X : ± 0.25 X.X° : $\pm 1^\circ$
X.XX : ± 0.20 X.XX° : $\pm 0.5^\circ$

DRAWN NAME: 2.0DC3-nPin H5.7 180度 PC2.8 L8.0 6T

SIZE	A4	SCALE	N:1	PROUCT NO.
REV	A	UNIT	mm	PROJECT

CHECKED: 陈超凡 2022/05/10 CHECKED: / / APPROVED: / /

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	4.00	6.00	24	22.00	24.00	42	40.00	42.00	60	58.00	60.00
8	6.00	8.00	26	24.00	26.00	44	42.00	44.00	62	60.00	62.00
10	8.00	10.00	28	26.00	28.00	46	44.00	46.00	64	62.00	64.00
12	10.00	12.00	30	28.00	30.00	48	46.00	48.00	66	64.00	66.00
14	12.00	14.00	32	30.00	32.00	50	48.00	50.00	68	66.00	68.00
16	14.00	16.00	34	32.00	34.00	52	50.00	52.00	70	68.00	70.00
18	16.00	18.00	36	34.00	36.00	54	52.00	54.00			
20	18.00	20.00	38	36.00	38.00	56	54.00	56.00			
22	20.00	22.00	40	38.00	40.00	58	56.00	58.00			