






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	①X3	产品外观及尺寸变更，图面升级整理图面	2025.07.18	阿树



Schematic(shorting)


- Specifications(规格):
- 1.Voltage rating(额定电压):DC 50V
 - 2.Current rating(额定电流):0.3A AC/DC
 - 3.Withstanding voltage(耐压值):500V AC/minute
 - 4.Operating force(操作力): T1-T2:250±100 T2-T3:300±100
 - 5.TRAVEL(开关行程): 2.0mm±0.3mm
 - 6.Mating cycles (使用寿命): ≥10000 cycles
 - 7.Temperature range(使用温度):-25℃~+85℃
 - 8.relative humidity(相对湿度):≤85%RH



SS13D07X X

L(mm)
2~12

Colour
Blank:Standard Black
R:Red



PCB LAYOUT

5	Contact piece	1	Imported phosphor copper	Single sided pressed silver
4	Terminal	4	Brass	Ag Plated
3	Base	1	KB Cold stamping plate	Yellow
2	Shell	1	Imported frosted material	
1	Housing	1	POM	
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
SLIDE SWITCH
PART NO.:
SS13D07XX
DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1