













REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		塑模变更, 图面升级整理图面	2025.05.28	阿树



PART NO.:

X10C25 XX G Z
① ② ③ ④

- ①Series Name: X10C25=1.00mm Pitch
- ②Number of terminals: XX=04-05PIN
- ③Plating : G: Gold Flash Over Nickel
- ④Z: positive needle

PIN	DIMENSIONS		
	A	B	C
04	3	5.03	11.10
05	4	6.03	12.10

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	FPC CONNECTOR
APPROVED		SIZE: A4	PART NO.:
			X10C25XXXX
			DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	2/2	A1