







SPECIFICATIONS


Current rating: 3A AC/DC
Voltage rating: 250V AC/DC
Contact resistance:20mΩ max.
Withstand voltage:1000V AC/min
Insulation resistance:500MΩ/min.
Temperature range:-25°C~+85°C

Material:

Part No:2~16
Post:Brass.Tin/plated
Base:LCP UL94V-0




Poles	PART NO.	Dimension mm		
		A	B	C
2	W-2502N02P-B200	2.50	5.90	10.00
3	W-2502N03P-B200	5.00	8.40	12.50
4	W-2502N04P-B200	7.50	10.90	15.00
5	W-2502N05P-B200	10.00	13.40	17.50
6	W-2502N06P-B200	12.50	15.90	20.00
7	W-2502N07P-B200	15.00	18.40	22.50
8	W-2502N08P-B200	17.50	20.90	25.00
9	W-2502N09P-B200	20.00	23.40	27.50
10	W-2502N10P-B200	22.50	25.90	30.00
11	W-2502N11P-B200	25.00	28.40	32.50
12	W-2502N12P-B200	27.50	30.90	35.00
13	W-2502N13P-B200	30.00	33.40	37.50
14	W-2502N14P-B200	32.50	35.90	40.00
15	W-2502N15P-B200	35.00	38.40	42.50
16	W-2502N16P-B200	37.50	40.90	45.00



P.B.C. Layout

TOLERANCE TABLE

.0	±0.30
.00	±0.15
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD						
CHECKED:	DATE:	TITLE: 2501SMT-XP 立贴 带扣						
DRAWN: LYF	DATE: 2022-07-11	PROD. NO.		W-2502NXXP-B200				
		UNIT	mm	SCALE	free			
		FILE NO.	Ckmtw-2501-B0006	REV.	A	JLX		