









REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	③X3	产品尺寸及外观变更, 图面升级整理图面	2025.07.19	阿树



3D VIEW

Specifications:
规格:
Voltage rating:100V AC/DC
额定电压: 100V AC/DC
Current rating:0.5A AC/DC
额定电流: 0.5A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃
Insulation resistance:500MΩ min
绝缘电阻: 500MΩ Min
Contact resistance:50mΩ Max
接触电阻: 50mΩ Max

PART NO.:

X0802 W V S-XX X S-LP V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Stright 180°
- ④Welding Way:S-SMT
- ⑤Row No.Pin No:XX-40-200P
- ⑥Height:A=4.7mm
- ⑦Special No:S-With positioning Column
- ⑧Material:LP-LCP UL 94V-0 BEIGE
- ⑨Plating:V01-Gold Flash

Poles	Dimensions					
	A	B	C	D	E	F
40	21.80	15.20	16.80	20.20	18.86	20.21
50	25.80	19.20	20.80	24.20	22.86	24.21
60	29.80	23.20	24.80	28.20	26.86	28.21
80	37.80	31.20	32.80	36.20	34.86	36.21
100	45.80	39.20	40.80	44.20	42.86	44.21
120	53.80	47.20	48.80	52.20	50.86	52.21
140	61.80	55.20	56.80	60.20	58.86	60.21
160	69.80	63.20	64.80	68.20	66.86	68.21
180	77.80	71.20	72.80	76.20	74.86	76.21
200	85.80	79.20	80.80	84.20	82.86	84.21

X0802WVS-XXXS-LPV0	LCP	Phosphor Bronze	X0802W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	①	MODEL TYPE:	0.8mm BTB Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X0802WVS-XXXS-LPV01
APPROVED		SIZE:	A4	DWG NO.:	