



LEFT LED  
YELLOW      RIGHT LED  
GREEN



PCB 参考图

e	LED	1	YELLOW	
d	LED	1	GREEN	
c	Shielding	1	Brass	Ni Plating
f	COVER	1	LCP+15% G.F UL94V-0	BLACK
b	Terminal	8	Phosphor Bronze	PLATING & COLOR
a	Housing	1	LCP+15% G.F UL94V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	Material & Plating
				Remark



3


REV	ECN NO.	DATE

### 主要参数:

1. 额度电压. 电流: 125V/1.5A max
2. 接触电阻: 40mΩ Max 初始态 100Ω Max 最终态
3. 绝缘电阻: 500MΩ Min
4. 试验条件: DC500V/5.0mA for 1 minute
5. 盐雾测试: 8±0.5H

### 其他要求:

1. 产品应无错装。漏装零件等现象;
2. 零件表面应无裂纹, 缺料, 飞边等现象, 表面镀层应光亮美观
3. 未注尺寸公差为±0.15mm



TOLERANCES 公差		DATE 日期	2011-03-11	浙江创都电子科技有限公司		
mm	±0.30	±				
.00±0.25		±				
.000±0.10		±		TITLE 品名	RJSP-32-DLSMT	
ANGLES	± 1°			SCALE 比例	1:1	UNIT 单位
				mm		SIZE A4
				Designed 设计		Checked 审核
					Approved 核准	
						SHEET OF

1

2

3

4