

增加料号		xushiyong 06.04.16	REVISION RECORD			
REV	ECO	DESCRIPTION	DRFT	CHKD		
△		原始版本	PEI/EI 06.03.05			
△		增加料号, 更改图号增加*UL HAXN*	xushiyong 07.02.02			

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD: COPPER ALLOY 0.20mm THICKNESS PLATING NI.
- 5.LED: OPTION.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.
- 6.LED RATINGS:FORWARD VOLTAGE:2.2 VOLTS TYPICAL.
REVERSE VOLTAGE:5 VOLTS MAXIMUM.

MECHANICAL:

- 1.DURRABILITY :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO +85°C.
2. OPERATION : 0°C TO 70°C.

MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68,SUBPART F.

PART NUMBER:

△ 2XNB-0312X1X13X

2XNB SERIES PCB JACK
(2XNB双层系列PCB接口)

SHIELD (屏蔽壳):

1-W/O SHIELD(非屏), 3-FULL SHIELD (全包)

PORTS (接口):

1-2X1 (一口), 2-2X2 (二口), 4-2X4 (四口)
6-2X6 (六口), 8-2X8 (八口)

EMI (弹片):

1-W/O EMI (无弹片)
2-W/ POSITIVE EMI (带正向弹片)

LED STYLE (LED 颜色类型):

1-L LED: GREEN, R LED: YELLOW (左绿右黄); 2-L LED: YELLOW, R LED: GREEN (左黄右绿)
3-L LED: GREEN, R LED: GREEN (双绿); 4-L LED: RED, R LED: GREEN (左红右绿)
5-L LED: YELLOW, R LED: YELLOW (双黄); 6-L LED: GREEN, R LED: RED (左绿右红)
7-L LED: GREEN+RED (双色灯), R LED: GREEN+RED (双色灯)
8-L LED: 黄绿双色灯, R LED: 黄绿双色灯

GOLD PLATING (镀金厚度)
1-F 1", 2-1.50", 3-30", 4-60",
5-150", 6-300", 7-500"

LOGO (标识):

0-W/O LOGO (无标识);

1-W/ HAXN (有HAXN标识)

2-W/ UL (有UL标识);

3-W/ HAXN, UL (有HAXN, UL)




COLOR (颜色): 1-BLACK (黑色);

PLASTIC (塑料):


1-PBT, 2-NYLON66 (尼龙66), 3-NYLON46 (尼龙46)

PIN STYLE (针类型):

1-ROUND PIN (圆针); 2-FLAT PIN (扁针)



双色灯输入对应发光颜色



PC Board Layout

— MM — (INCH)		设计	日期
— 公差 —		审核 GANBO	06.03.05
MM		批准 xushiyong	06.03.06
0 ± 0.20	±	材料:	
.00 ± 0.15	±	数量:	
.000 ± 0.075	±	表面处理:	
角度		比例:	
第三角视图			

浙江创都电子科技有限公司

RJ59B-2X1+LED-SC

图号:

料号:

不 按 比 例

第 页