

A

B

C

D

E

正面图

A

B





C

D

E

F

G



## 技术参数 (SPECIFICATION):

温度范围 (TEMPERATURE RANGE): -40 ~ +70 °C  
 额定电压 (VOLTAGE RATING): 125V  
 额定电流 (CURRENT RATING): 1.5A  
 接触电阻 (CONTACT RESISTANCE): ≤ 30mΩ  
 绝缘电阻 (INSULATION RESISTANCE): ≥ 500MΩ  
 耐压 (DIELECTRIC STRENGTH): 500V AC / (50Hz) / Min  
 插拔力 (MATING AND UNMATING FORCE): 3 ~ 20N  
 寿命 (DURABILITY): 750 CYCLES MIN

Table 1

X	Terminal Plating
0	Au $1\mu$ " Plating
1	Au $2\mu$ " Plating
2	Au $3\mu$ " Plating
3	Au $6\mu$ " Plating
4	Au $10\mu$ " Plating
5	Au $15\mu$ " Plating
6	Au $30\mu$ " Plating

## Material &amp; Plating

## Part NO.:

RCH5604-QS-X-XX-10P10C

Material & Color  
Table 2

XX	Material/Color
BB	PBT/BLACK
BW	PBT/WHITE
AB	PA/BLACK
AW	PA/WHITE
OO	OTHER/OTHER

3	后 盖	PA	1	BLACK	
2	插 针	PHOSPHOR BRONZE	10	AU	
1	塑 座	PA	1	BLACK	
序号	名 称	材 料	数 量	镀 层/颜色	备 注

浙江创都电子科技有限公司

## 网络插座外形图

绘 图:

品 名:

RJ58-10P10C-QSWL

日 期:

料 号:

审 核:

型 号:

RJ45

日 期:

图 号:

核 准:

角 度:

1:1

日 期:

页 面:

纸 张: A4

核 准:

版 本:

单 位: mm

日 期:

比 例:

复 印

禁 止 在 图 上 随 意 涂 改

新 出 版 发 行

变 更 单 号

绘 制

日 期

版 次

变 更 履 历

核 准:

日 期:

复 印

该 图