

1	2	3	4	5	6	7	8																															
					版次		内容	申请人	日期																													
A									A																													
B									B																													
C					规格: 接触电阻: ≤20mΩ Max 绝缘电阻: ≥500MΩ 额定电压: 100V, AC DC 额定电流: 1.0A AC DC 耐受电压: 500V AC/min 温度范围: -25~85℃。 基座: LCP(米黄色) UL94V-0 吸料盖: LCP(米黄色) UL94V-0 铜针: 黄铜(亮锡或雾锡或镀金)				C																													
D					产品料号: 1502B-WV-S-*M1-*-*1 孔位: 2P-16P 塑料材料: M1=LCP(米黄色) 颜色: 1. 米黄色 包装: R=卷装 电镀: A=亮锡、B=雾锡、C=镀金				D																													
E					浙江创都电子科技有限公司 <table><tr><td>产品名称:</td><td colspan="3">MXB1.5-*PLT-WK</td><td rowspan="2">绘图:</td></tr><tr><td>产品料号:</td><td colspan="3"></td></tr><tr><td>第一视图</td><td>比例</td><td>单位</td><td>用途</td><td>审核:</td></tr><tr><td></td><td>1:1</td><td>mm</td><td>客户</td><td>批准:</td></tr><tr><td colspan="4"></td><td>版次:A01</td></tr><tr><td colspan="4"></td><td>日期:2019/09/20</td></tr></table>				产品名称:	MXB1.5-*PLT-WK			绘图:	产品料号:				第一视图	比例	单位	用途	审核:		1:1	mm	客户	批准:					版次:A01					日期:2019/09/20	E
产品名称:	MXB1.5-*PLT-WK			绘图:																																		
产品料号:																																						
第一视图	比例	单位	用途	审核:																																		
	1:1	mm	客户	批准:																																		
				版次:A01																																		
				日期:2019/09/20																																		
1	2	3	4	5	6	7	8																															