




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.06	阿树





RECOMMENDED P.C.B LAYOUT

规格Specifications:
额定负荷 Rating : DC 12V/50mA
接触电阻Contact Resistance: 100mΩ max
绝缘电阻Insulation resistance :DC100V 60S 100MΩ min
抗电强度Dielectric strength :AC250V(50~60HZ) 60S min
寿命试验Operating Life :100,000cycles

PAPT NO	TS-1199A-X-X
Operating Force	B:160gf B1:200gf C:280gf
Height	A:4.3 B:5.0



CIRCUIT DIAGRAM



⑤	Cover	1	LCP	BLACK
④	Actuator	1	Silicone	
③	Contact	1	Stainless Steel	Ag-Plated
②	Terminal	2	Brass	Ag-Plated
①	Housing	1	LCP	BLACK
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树
UNIT: mm/in
SIZE: A4

VIEW:

MODEL TYPE:
TACT SWITCH
PART NO.:
TS-1199A-X-X
DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1