

REVISION RECORD					
REV	ECO	DESCRIPTION	DRFT	CHKD	
△		原始版本		PEILEI	05.08.10
△		增加料号,更改图号增加"HAXN"		xushiyong	07.02.05

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.

ELECTRICAL:


- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

- 1.DURRABILITY :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO $+85^{\circ}\text{C}$.
 2. OPERATION : 0°C TO 70°C .
- MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68,SUBPART F.



PART NUMBER:

△ 5224-011880X1XX

5224 SERIES PCB JACK
(5224系列PCB接口)

SHIELD (屏蔽壳) :1-W/O SHIELD (非屏)

2-HALF SHIELD (半包) ;3-FULL SHIELD (全包)

PORTS (插口) :

1-1X1 (一口) . 4-1X4 (四口) . 8-1X8 (八口)

POSITIONS (金针位置) :

4-4POSITIONS (4P) ;6-6POSITIONS (6P)

8-8POSITIONS (8P) ;0-10POSITIONS (10P)

CONTACTS (金针根数) :4-4CONTACTS (4C)

6-6CONTACTS (6C) . 8-8CONTACTS (8C) . 0-10CONTACTS (10C)

PEG/TAB (边定位铁脚) :

0-W/O PEG (无铁脚) . 1-FRONT PEG 3.05 (前脚3.05) . 2-FRONT PEG3.68 (前脚3.68)

3-FRONT PEG4.57 (前脚4.57) . 4-BACK PEG3.05 (后脚3.05)

GOLD PLATING (镀金厚度)

1-F U" . 2-1.5U" . 3-3U" . 4-6U" .
5-15U" . 6-30U" . 7-50U"

LOGO (标识) :

0-W/O LOGO (无标识) .

1-W/ HAXN (有HAXN标识)


2-W/ UL (有UL标识) .

3-W/ HAXN. UL (有HAXN. UL)

COLOR (颜色) :1-BLACK (黑色) . 2-WHITE (白色)

PLASTIC (塑料) :

1-PBT. 2-NYLON66 (尼龙66) . 3-NYLON46 (尼龙46) .



PC Board Layout

DETACHED LISTS		设计	日期	浙江创都电子科技有限公司	
一 般 公 差 栏		审核 GANBO	日期 05.08.10		
MM	±	批准 xushiyong	日期 05.08.10	RJ5224-8P8C-QSWL	
.0 ± 0.20	±	材料:			
.00 ± 0.15	±	数量:		图号:	
.000 ± 0.075	±	表面处理:		料号:	
角度 ± 0.01°		比例:		不 按 比 例	第 页
第三角视图					