





1 2 3 4 5 6 7 8 9 10 11

A
B
C
D
E
F
G
禁止图面上随意涂改

A/0
版次
新出版发行
变更履历
变更单号
绘 制
日 期
核 准
日 期



BOTTOM VIEW



PCB LAYOUT (BOTTOM VIEW)
RECOMMENDED

技术参数 (SPECIFICATION):

温度范围 (TEMPERATURE RANGE): -40~+70 °C
额定电压 (VOLTAGE RATING): 125V
额定电流 (CURRENT RATING): 1.5A
接触电阻 (CONTACT RESISTANCE): ≤ 30mΩ
绝缘电阻 (INSULATION RESISTANCE): ≥ 500MΩ
耐压 (DIELECTRIC STRENGTH): 1000V AC/(50HZ)/Min
插拔力 (MATING AND UNMATING FORCE): 3~20N
寿命 (DURABILITY): 750 CYCLES MIN

材料 (MATERIAL):

塑 座 (HOUSING) PBT/PA (UL94V-0)
插 针 (CONTACT) : PHOSPHOR BRONZE Ø0.46mm
镀 层 (PLATING) : GOLD PLATING OVER NICKEL

复 印

网络插座外形图

浙江创都电子科技有限公司

绘 图:

品 名:

网络插座

日 期:

料 号:

RJ59-1x2-QSWL

审 核:

型 号:

RJ45

核 准:

图 号:

1

日 期:

页 面:

1 of 1

版 本:

单 位:

mm

比 例:

1:1

纸 张:

A4

