


This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H. wei	19/03/17	19/03/17



1 Electrical电气性能


- 1.1 Impedance特性阻抗: 50 Ω
1.2 Frequency频率范围: DC~6GHz
1.3 VSWR电压驻波比: ≤1.30
1.4 Insulation resistance绝缘电阻: ≥5000M Ω
1.5 Dielectric withstanding voltage介质耐压: 1000V

No.	Product Model	Length L (mm)
1	HL-SMAM-086-SMAM-100MM	100mm
2	HL-SMAM-086-SMAM-150MM	150mm
3	HL-SMAM-086-SMAM-200MM	200mm
4	HL-SMAM-086-SMAM-300MM	300mm
5	HL-SMAM-086-SMAM-1000MM	1000mm

No.	Description	Qty.	Note
1	SMA Male Conn.	2	
2	RG086 Cable	1	
3	Black Color Heat Shrinkable Tube	2	
4	Lable White Color	1	

DRAWN:	H. wei	19/03/17
ENGINEER:	L. yu	19/03/17
APPROVED:	W. yi	19/03/17
TOLERANCES UNLESS OTHERWISE SPECIFIED		
	X	±0.50
	.X	±0.20
	.XX	±0.10
	ANGLES	±1°

PART NO:	HL-SMAM-086-SMAM-1000MM
----------	-------------------------

 HenryTech			
 DIMENSION IN MILLIMETERS (mm)			
SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A

Notes:

1. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
2. CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY