


















<p style="text-align: center;">1</p>  <p style="text-align: center;">2</p>  <p style="text-align: center;">3</p>  <p style="text-align: center;">4</p> 	<p style="text-align: center;">1</p>  <p style="text-align: center;">2</p>  <p style="text-align: center;">3</p>  <p style="text-align: center;">4</p> 	<p style="text-align: center;">1</p>  <p style="text-align: center;">2</p>  <p style="text-align: center;">3</p>  <p style="text-align: center;">4</p> 	<p style="text-align: center;">1</p>  <p style="text-align: center;">2</p>  <p style="text-align: center;">3</p>  <p style="text-align: center;">4</p> 
<p>A</p> <p>B</p> <p>C</p> <p>D</p>	<p>REV</p>	<p>ECN NO.</p>	<p>DATE</p>
<p>A</p> <p>B</p> <p>C</p> <p>D</p>	<p>REV</p>	<p>ECN NO.</p>	<p>DATE</p>

主要参数:

1. 额度电压. 电流: 125V/1.5A max
2. 接触电阻: 40mΩ Max 初始态 100Ω Max 最终态
3. 绝缘电阻: 500MΩ Min
4. 试验条件: DC500V/5.0mA for 1 minute
5. 盐雾测试: 8±0.5H

其他要求:

未注尺寸公差为±0.15mm



PCB 参考图

<p>e LED 1 YELLOW</p> <p>d LED 1 GREEN</p> <p>c Shielding 1 Brass Ni Plating</p> <p>f COVER 1 LCP+15% G.F UL94V-0 BLACK</p> <p>b Terminal 8 Phosphor Bronze PLATING & COLOR</p> <p>a Housing 1 LCP+15% G.F UL94V-0 BLACK</p>	<p>NO. PART NAME Q'TY MATERIAL Material & Plating Remark</p>	<p>RoHS Compliant</p>	<p>浙江创都电子科技有限公司</p>
--	--	------------------------------	----------------------------

<p>TOLERANCES 公差</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 50%;">mm</td> <td style="width: 50%;">±</td> </tr> <tr> <td>.0±0.30</td> <td>±</td> </tr> <tr> <td>.00±0.25</td> <td>±</td> </tr> <tr> <td>.000±0.10</td> <td>±</td> </tr> <tr> <td colspan="2">ANGLES ± 1°</td> </tr> </table>		mm	±	.0±0.30	±	.00±0.25	±	.000±0.10	±	ANGLES ± 1°		<p>DATE 日期 2011-03-11</p>	<p>MATERIAL</p>	<p>TITLEL 品名 RJSP-32CB4.2WLPBSMT</p>
mm	±													
.0±0.30	±													
.00±0.25	±													
.000±0.10	±													
ANGLES ± 1°														
<p>THIRD ANGLE PROJECTION</p>		<p>SCALE 比例 1:1</p>	<p>UNIT 单位 mm</p>	<p>ART NO. 料号 Checked 审核 Approved 核准 SHEET OF</p>										