

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.05.22	
A2	N/A	A2X2		2025.09.05	

Specifications:

- Voltage rating:250VAC/DC
250V AC/DC
- Current rating:3A AC/DC
: 3A AC/DC
- Withstanding voltage:500V AC/minute
500V AC/
- Temperature range: -55 -+105
-55 -+105
- Insulation resistance:1000MΩ MIN
:1000MΩ MIN
- Contact resistance:30mΩ Max
30mΩ Max

Material:

- Rubber core:PBT UL94V-0
PBT UL94V-0
- The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
SPCC-SD, / /
- Terminal:Copper alloy

PART NO.:

X01 XX W X X X X

Series NO.

Row No.Pin No.XX-09;15;25;37

Welding Board Angle :W-Male





T Tradutional C Car-pin

Planting Categoty: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AuSn'

Color:B-BLACK W-White BL-Blue

1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	18.00	24.99	30.80	19.28
15	26.50	33.32	39.20	27.51
25	40.00	47.04	53.05	41.28
37	56.60	63.50	69.40	57.71

	TYPE-1:	TYPE-2:	TYPE-3:	TYPE-4:
				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW: 	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X01XXWXXXX
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2