










Product NO. DS1-01XXM0002-A				
REV	DESCRIPTION	DMN	DATE	APPROVEN
A	First issue	Gavin	2023/03/25	John kine



建议开板尺寸



- 技术要求:
- 1>标准阻抗:50 OHM.
 - 2>频率范围:0~6 GHz.
 - 3>电压定额值:335V_{r.m.s}海平面最大值.
 - 4>电介质耐压:750V_{r.m.s}海平面最小值.
 - 5>电压驻波比:1.50 MAX.
 - 6>螺纹扭力:15 in-lbs MIN.
 - 7>机械耐插:500次插拔.
 - 8>绝缘体与铜件保持力>2kg

型号 Coding	图示 Graphics	颜色 Colour	料号 Product NO.	型号 Coding	图示 Graphics	颜色 Colour	料号 Product NO.
A		Black黑色 RAL9005	DS1-0101M0002-A	H		Violet紫罗兰 RAL4003	DS1-0108M0002-A
B		White白色 RAL9001	DS1-0102M0002-A	I		Beige米黄色 RAL1001	DS1-0109M0002-A
C		Blue蓝色 RAL5005	DS1-0103M0002-A	K		Curry咖喱黄 RAL1027	DS1-0110M0002-A
D		Bordeaux 酒红紫RAL4004	DS1-0104M0002-A	L		Carmine Red 胭脂红 RAL3002	DS1-0111M0002-A
E		Green绿色 RAL6002	DS1-0105M0002-A	M		Pastel Orange 淡橙色 RAL2003	DS1-0112M0002-A
F		Brown棕色 RAL8011	DS1-0106M0002-A	N		Pastel Green 浅绿色 RAL6019	DS1-0113M0002-A
G		Gray灰色 RAL7031	DS1-0107M0002-A	Z		Water Blue 水蓝色 RAL5021	DS1-0114M0002-A



东莞市德索精密工业有限公司
Dongguan Dosin Precision Industry Co., Ltd

DRAWN Gavin		View		Name:		FAKRA 公头线端锁板178线	
CHECKED		UNIT		SIZE A		Product NO. DS1-01XXM0002-A	
APPROVALS John kine		SCALE		DateTime 2023/03/25		CAD FILE D/company drawings/BD	
SHEET: 1 OF 1		REV A		G		G	