








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		产品pin位图表A尺寸修正，图面升级整理图面	2025.07.14	阿树



- SPECIFICATIONS
- Voltage rating:100V AC/DC
 - Current rating:1.5A AC/DC
 - Withstanding Voltage:500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥500MΩ
 - Contact resistance:≤20mΩ
 - After environmental testing:≤40mΩ

PART NO.:

X1515 W R S-2xXX-LP SW
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
2.Category:W-Wafer
3.Welding Board Angle:R-Straight 90°
4.WELDING Way:S-SMT
5.Row No.Pin No:2xXX-2x04~2x14Pin
6.Material:LP-LCP UL94V-0
7.Plating:SW-Matte Tin Plated

Poles	Dimensions(mm)			
	A	B	C	D
2x04	4.50	10.30	7.40	8.95
2x05	6.00	11.80	8.90	10.45
2x06	7.50	13.30	10.40	11.95
2x07	9.00	14.80	11.90	13.45
2x08	10.50	16.30	13.40	14.95
2x09	12.00	17.80	14.90	16.45
2x10	13.50	19.30	16.40	17.95
2x11	15.00	20.80	17.90	19.45
2x12	16.50	22.30	19.40	20.95
2x13	18.00	23.80	20.90	22.45
2x14	19.50	25.30	22.40	23.95

X1515WRS-2xXX-LPSW	LCP	Phosphor Bronze	Brass	X1515H-A
PART NO	Material	Material(Pin)	Material (Solder Tabs)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	1.5mm Crimp Style Connector
PART NO.:	X1515WRS-2xXX-LPSW
DWG NO.:	







1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.07.14	阿树



2*04P~2*05P Shape
Scale 1:1

2*06P~2*09P Shape
Scale 1:1

2*10P~2*14P Shape
Scale 1:1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.5mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1515WRS-2xXX-LPSW
APPROVED		SIZE: A4	DWG NO.:

1

2

3

4