

## Features

- Panel Mounted
- Gold Plated contacts
- Nylon body

## RS PRO 6.35mm Gold Plated Jack Socket

RS Stock No.: 2795430



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Theis 6.35mm mono jack socket has a robust nylon body and gold plated contacts. It has a metal front nut, bezel and 2 washers for panel fixing.

%" Jack Sockets are often used in musical instruments, found on amplifiers and electric guitars, keyboards and drum kits. Whether in a professional studio or stage environment, or for home use, jack connectors are a staple connector for musicians and engineers. They also have applications in commercial public address systems and industrial systems.

## General Specifications

Gender	Female
Size	6.35mm
Colour	Black

## Mechanical Specifications

Max. Panel Thickness	4.3mm
Termination method	Solder tags
Body moulding	Nylon
Contacts	Gold plated

## Electrical Specifications

Maximum Current	5A
Dielectric Withstand Voltage	2000V DC Min
Nominal Contact Resistance	<50mΩ
Life (minimum)	10,000+ operations
Temperature Rating	-10°C to +70°C

## Approvals

Standards Met	RoHS
---------------	------

## Similar Products

