



Datasheet 20 Way universal IDC Cable skt, 29.97mm L

RS Stock number 471-216



Specifications:

Contact: Phosphor bronze

Plating: Gold plated over nickel

Insulator Material: PBT & glass-fibre reinforced grey

colour

Current rating: 1A dc Max.

Insulator Resistance: 1000M ohm min. at 500V dc

Contact Resistance: 30M ohm max. at 6V dc 300mA


Dielectric withstanding voltage: 500V ac for one minute

Operating Temperature: -55°C ~ +105°C

Approval: UL E163369







DACITION		
POSITION	A	В
6	12.18	5.08
8	14.72	7.62
10	17.26	10.16
12	19.80	12.70
14	22.34	15.24
16	24.88	17.78
20	29.96	22.86
24	35.04	27.94
26	37.58	30.48_
30	42.66	35 <u>.5</u> 6
34	47.74	40.64
36	50.28	43.18
40	55.36	48.26
44	60.44	53.34
50	68.06	60.96
56	75.68	68.58
60	80.76	73.66
62	83.30	76.20
64	85.84	78.74