

Datasheet

RS Pro Uninsulated Tin Plated Crimp Ring Terminal, M6 Stud Size, 1.5mm² to 2.5mm², 16AWG to 14AWGRS Stock No: **208-2593****Features and Benefits**

- Sheet formed terminal
- Copper contacts
- Uninsulated

Specifications:

Contact Material	Copper
Contact Plating	Tin
Inner Ring Diameter	6.4 mm
Insulation	Uninsulated
Maximum Wire Size (AWG)	14 AWG
Maximum Wire Size (mm ²)	2.5 mm ²
Minimum Wire Size (AWG)	16 AWG



ENGLISH

Minimum Wire Size (mm ²)	1.5 mm ²
Outer Ring Diameter	10.5 mm
Overall Length	21.0 mm
Stud Size	1/4 in
Thickness	0.8 mm
Wire Size	16 to 14 AWG
Temperature Rating	+75°C
Amperage Rating	18 to 30 A
Voltage Rating	600 V
Type	Butted Seam Barrel