





REV. 1.0	SCALE 2X	UNIT mm	ALSO ACCEPTS CR2020 CR2025 CR2032	MATERIAL 0.25 PHOSPHOR BRONZE FINISH NICKEL-PLATED
TOLERANCES DECIMAL ANGULAR	± 0.1 $\pm 1^\circ$		COATING PARAMETERS 4μm	TEMPERATURE RANGE - 40°C ~ 270°C
DRAW JINZHI	APPROVAL GWEN	COLOUR SILVERY	PART NAME COIN CELL RETAINERS	PART NO KST-2018B