





B		F	
DIMENSION (尺寸)			
No of conductors (导体数目)	N	10	
Pitch (间距)	▲P	0.5	±0.05
Span (总间距)	▲SP	4.5	±0.07
Width (宽度)	▲W	5.5	±0.08
Margin (边距)	▲M	0.5	±0.07
	/	/	/
Total length (总长)	▲TL	100	±2.0
Insulator length (绝缘段长)	IL	94	/
Insert Thickness (插接端厚度)	T	0.30	±0.05
Surface Thickness (线身厚度)	ST	0.12	±0.05
Strip length (裸铜长度)	▲S1	3.00	±0.5
	▲S2	3.00	±0.5
Supporting Tape length (补强板长度)	B1	5.00	±1.0
	B2	5.00	±1.0
Strip Slant (线口倾斜)	A1	≤0.3	
Punch Slant (冲孔倾斜)	A2	≤0.3	

Material List (辅料清单)			
NO	ITEM(项目)	SPEC(规格)	QTY(数量)
1			
2			
3			
4			
5			
6			



		STRUCTURE (构造)		REMARK (备注)
NO	ITEM (项目)	SPECIFICATION (规格)		
1	INSULATION (胶膜)	Printed 印字 (43um)		/
		AWM 20624 80C 60V VW-1		
2	SUPPORTING TAPE (本强板)	Blue 蓝色 (225um)		/
3	CONDUCTOR 导体	Thickness (厚度)	0.035	±0.005
		Width (宽度)	0.3	±0.03
4	CONDUCTOR 导体镀层	PLATED (电镀)	Sn (40 μ " 锡)	MIN
			/	/

Δ	新图制定	Yem	2025. 11. 21	一般公差 (TOLERANCE)
版次	变更内容	申请人	发行日期	$X \pm 50$ $.XX \pm 10$ $X \pm 20$ $.XXX \pm 05$ $ANGLES$ $\pm 1^\circ$

品名 (ITEM)		制图 (DR)	
0.5 FCC反向排线-10P T1=100mm		Kenny	
料号 (DWG.NO)		校对 (CHKD)	
MTB-DT10-0100N-3/3/5/5		Thomas	
比例 (SCALE)		审核 (APRD)	
1:1		Dawlin	
单位 (UNITS)	张数 (SHEET)	SIZE	REV
mm	1 OF 1	A4	A
			