






PIN	DIM A	DIM B	DIM C
2P	10.00	6.10	2.50
3P	12.50	8.60	5.00
4P	15.00	11.10	7.50
5P	17.50	13.60	10.00
6P	20.00	16.10	12.50
7P	22.50	18.60	15.00
8P	25.00	21.10	17.50
9P	27.50	23.60	20.00
10P	30.00	26.10	22.50
11P	32.50	28.60	25.00
12P	35.00	31.10	27.50
13P	37.50	33.60	30.00
14P	40.00	36.10	32.50
15P	42.50	38.60	35.00
16P	45.00	41.10	37.50



SPECIFICATION

- 1.Contact resistance: $\leq 10\text{M}\Omega$
2. Insulation resistance: $\geq 1000\text{M}\Omega$
3. Rated voltage: 250 V AC DC
4. Rated current: 3.0 A AC DC
5. Withstand Voltage: 1000V AC/minute
6. Temperature Range : $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

2	插针	铜	镀镍锡	
1	基座	LCP	本色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名	针座	
			TITLE		
			料 号	HCZZ0021-16	
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列 SCALE	1 : 1	
X. xxx ±0.10 X. xx ±0.20 X. x ±0.30 X. xx° ±1° X. x° ±3° X. ° ±5°			单 位 UNIT	MM	制 图 DRAW
			张 数 PART NO	1 OF 1	审 核 CHECKED
			版 本 REV	A	夏 操 云
			批 准 APPROVE	赵 亮 亮	