





CONTACTS:

0.15PHOSPHOR BRONZE GOLD PLATING



REV.	SCALE	UNIT	ALSO ACCEPTS	MATERIAL	PPA
1.0	3X	mm	CR2020 CR2025 CR2032	FINISH	WITH
TOLERANCES	DECIMAL	ANGULAR	COATING PARAMETERS	TEMPERATURE RANGE	VOLTAGE PARAMETERS
	± 0.1	± 1°	UL 94V-0	- 40°C ~ 270°C	270V
DRAW	APPROVAL	COLOUR	PART NAME	PART NO	
JINZHI	GWEN	SILVERY	BATTERY HOLDERS	KST-2011	