


E		F	
DIMENSION (尺寸)			
No of conductors (导体数目)	N	10	
Pitch (间距)	▲ P	0.5	±0.05
Span (总间距)	▲ SP	4.5	±0.07
Width (宽度)	▲ W	5.5	±0.08
Margin (边距)	▲ M	0.5	±0.07
	/	/	/
Total length (总长)	▲ TL	50	±2.0
Insulator length (绝缘胶长)	IL	44	/
Insert Thickness (插接端厚度)	T	0.30	±0.05
Suface Thickness (线身厚度)	ST	0.12	±0.05
Strip Length (裸铜长度)	▲ S1	3.00	±0.5
	▲ S2	3.00	±0.5
Supporting Tape length (补强板长度)	B1	5.00	±1.0
Strip Slant (线口倾斜)	B2	5.00	±1.0
Punch Slant (冲孔倾斜)	A2	≤0.3	

E		F	
DIMENSION (尺寸)			
No of conductors (导体数目)	N	10	
Pitch (间距)	▲ P	0.5	±0.05
Span (总间距)	▲ SP	4.5	±0.07
Width (宽度)	▲ W	5.5	±0.08
Margin (边距)	▲ M	0.5	±0.07
	/	/	/
Total length (总长)	▲ TL	50	±2.0
Insulator length (绝缘胶长)	IL	44	/
Insert Thickness (插接端厚度)	T	0.30	±0.05
Surface Thickness (线身厚度)	ST	0.12	±0.05
	Strip length (裸铜长度)	▲ S1	3.00 ±0.5
Supporting Tape length (补强板长度)		▲ S2	3.00 ±0.5
	B1	5.00	±1.0
	B2	5.00	±1.0
Strip Slant (线口侧斜)	A1	≤0.3	
Punch Slant (冲孔侧斜)	A2	≤0.3	

Material List (辅料清单)		
NO	ITEM(项目)	QTY(数量)
1		
2		
3		
4		
5		
6		



		STRUCTURE (构造)		REMARK (备注)
NO	ITEM (项目)	SPECIFICATION (规格)		
1	INSULATION (胶膜)	Printed 印字 (43um)		/
		AWM 20624 105C 60V VW-1		
2	SUPPORTING TAPE (补强板)	Blue 蓝色 (223um)		/
3	CONDUCTOR 导体	Thickness (厚度)	0.035	±0.001
		Width (宽度)	0.30	±0.03
4	CONDUCTOR 导体镀层	PLATED (电镀)	Sn (40 μ " 锡)	MIN
			/	/

MINTRON TECHNOLOGY CO.,LTD.				
品名 (TITLE)	0.50 FCC排线 10P TL=50mm			
料号 (PWC.A0)				
M7A-DT10-0050N-3/3/5/5				
比例 (SCALE)	1:1	单位 (UNITS)	mm	
				
				
		张数 (SHEET)	1 OF 1	
		审核 (APPD)	Dawin	
		校对 (CHKD)	Thomas	
		制图 (DRS)	Kenny	
F				