



R

P.C.B LAYOUT(Copper-side view)



Rating: 0.5A 30V DC
 Contact Resistance: 100 mΩ Max.
 Operating temperature: -20°C ~ 70°C
 Operating force: 3~20N
 Operating Life: 5,000cycles

②	Terminal	3	Phosphor bronze	Au Plating	
①	Housing	1	Nylon	Black	
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING
APPROVALS		DATE		hro®	
DRAWN	J.X.Zhang	2013/11/11			
CHECKED				TITLE:	PHONE JACKES
APPROVALS				PART NO.	DC-055D-3A
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm
		10~30	±0.20		SCALE: 1:1
		5~10	±0.15	±2°	PROJ:
		~ 5	±0.10	DRAWING NO.	SHEET 1 OF 1

—	A	—	NEW	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.
				APPRO.	