



PCB LAYOUT


TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

Specification

Insulator Material: Polysetr,UL94V-0
Standard:Nylon-6T

Contact Material: Brass
Contact plated: Gold Over Nickel

Current Rating : 1Amp
Contact Resistance:20 Milliohms Max
Insulation Resistance : 1000MΩ Min.
Dielectric withstanding Voltage:AC 500V
Operation Temperature : -40℃ -- +105℃



APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD						
CHECKED:	DATE:	TITLE: 210-1S-2*XP 3.0/1.0/1.8						
DRAWN: LYF	DATE: 2008-04-29	CLIENT P/N		/				
		UNIT	mm	SCALE	free			
		FILE NO.		Ckmtw-210-10002		REV.	A	