

DIMENSION (尺寸)			
No of conductors (导体数目)	N	YY	
Pitch (间距)	▲ P	0.5	±0.05
Span (总间距)	▲ SP	0.5*(YY-1)	±0.07
Width (宽度)	▲ W	0.5*(YY+1)	±0.08
Margin (边距)	▲ M	0.5	±0.07
	/	/	/
Total length (总长)	▲ TL	100	±2.0
Insulator length (绝缘胶长)	IL	92	/
Insert Thickness (插接端厚度)	T	0.30	±0.05
Surface Thickness (线身厚度)	ST	0.12	±0.05
Strip Length (裸铜长度)	▲ S1	4.00	±0.5
	▲ S2	4.00	±0.5
Supporting Tape length (补强板长度)	B1	8.00	±1.5
Strip Slant (线口倾斜)	B2	8.00	±1.5
Punch Slant (冲孔倾斜)	A1	≤0.3	
	A2	≤0.3	