






NOTES:

1. MATERIAL:

HOUSING: GLASS FILLED PPA, UL94V-0,
TERMINAL: 0.15mm PHOSPHOR BRONZE, NICKEL PLATED



REV. 1.0	SCALE 2X	UNIT mm	ALSO ACCEPTS CR2020 CR2025CR2032	MATERIAL PPA
TOLERANCES DECIMAL ANGULAR	± 0.35 ± 1°		FLAME RATING UL 94V-0	COLOR/FINISH BLACK
DRAW JINZHI	APPROVAL GWEN	COLOUR SILVERY	TEMPERATURE RANGE - 40 °C ~ 270 °C	VOLTAGE PARAMETERS 270V
			PART NAME BATTERY HOLDERS	PART NO KST-2002