

1

2

3

4

RoHS


Specifications(规格):

- 1.Impedance(特性阻抗): 50Ω;  
2.Frequency (工作频率): DC~6GHz;  
3.VSWR (电压驻波比): 1.60 Max.  
4.Insulation resistance(绝缘阻抗): ≥100MΩ;  
5.Dielectric withstand voltage (介质耐电压): 800V AC;  
6.Mating cycles (耐久性): ≥25 cycles;  
7.Retention force latch(保持力): ≥110N;  
8.Temperature range(使用温度): -40℃~+105℃;


PART NO.:

X Z X R X - M2F-XXXX-M2F- X X  
① ② ③ ④ ⑤

- ① Cable TYPE:  
3: RG174  
4: 1.5DS  
7: Dacar302/RTK031  
8: RG174LL  
② Successive number: 1~Z  
③ Length (mm): 1000=1000mm  
④ Coding A: A~Z  
⑤ Coding B: A~Z



接点表(Wiring Table)



| PART NO.              | Length (mm/inch) | TOLERANCES (mm/inch) |
|-----------------------|------------------|----------------------|
| XZ7RV-M2F-500-M2F-ZZ  | 500 [19.685]     | ±10 [0.394]          |
| XZ7RV-M2F-1000-M2F-ZZ | 1000 [39.370]    | ±15 [0.591]          |
| XZ7RV-M2F-2000-M2F-ZZ | 2000 [78.740]    | ±20 [0.787]          |
| XZ7RV-M2F-3000-M2F-ZZ | 3000 [118.110]   | ±30 [1.181]          |
| XZ7RV-M2F-4000-M2F-ZZ | 4000 [157.480]   | ±60 [2.362]          |

|     |           |                                                    |      |      |
|-----|-----------|----------------------------------------------------|------|------|
| 2   | Connector | Vertical Double MINI FAKRA Female Connector,Z Code | 2SET | R版   |
| 1   | Cable     | RTK031 Cable PVC OD3.30 Black,-40~105℃             | 2PCS |      |
| NO. | NAME      | SPEC.                                              | Q'TY | NOTE |

|                                      |    |             |                                                               |
|--------------------------------------|----|-------------|---------------------------------------------------------------|
| DESIGN                               | 希文 | VIEW:       | MODEL TYPE: Assembly cable, Vertical,Double MINI FAKRA series |
| CHECKED                              |    | UNIT: mm/in | PART NO.: XZ7RV-M2F-XXXX-M2F-ZZ                               |
| APPROVED                             |    | SIZE: A4    | DWG NO.: X-XZ7RV-M2F-XXXX-M2F-ZZ                              |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |    |             | SCALE: N/A                                                    |
|                                      |    |             | PAGE: 1/1                                                     |
|                                      |    |             | REVISION: A0                                                  |

1

2

3

4