

RoHS

Specifications(规格):

- 1.Impedance(特性阻抗) : 50Ω;
- 2.Frequency (工作频率) : DC~6GHz;
- 3.VSWR (电压驻波比) : 1.60 Max.
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Retention force latch(保持力) : ≥110N;
- 8.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

X Z X R X - M2F-XXXX-M2F- X X
 ① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302/RTK031
8: RG174LL
- ② Successive number: 1~Z
- ③ Length (mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z

接点表(Wiring Table)

A端(A port)	Cable	B端(B port)
A1 [Pin shell]	Conductor Braid	Pin Shell] B1
A2 [Pin shell]	Conductor Braid	Pin Shell] B2

PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ7RV-M2F-500-M2F-ZZ	500 [19.685]	±10 [0.394]
XZ7RV-M2F-1000-M2F-ZZ	1000 [39.370]	±15 [0.591]
XZ7RV-M2F-2000-M2F-ZZ	2000 [78.740]	±20 [0.787]
XZ7RV-M2F-3000-M2F-ZZ	3000 [118.110]	±30 [1.181]
XZ7RV-M2F-4000-M2F-ZZ	4000 [157.480]	±60 [2.362]

2	Connector	Vertical Double MINI FAKRA Female Connector,Z Code	2SET	R版
1	Cable	RTK031 Cable PVC OD3.30 Black,-40~105℃	2PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

DESIGN	希文	VIEW:	MODEL TYPE: Assembly cable, Vertical,Double MINI FAKRA series
CHECKED		UNIT: mm/in	PART NO.: XZ7RV-M2F-XXXX-M2F-ZZ
APPROVED		SIZE: A4	DWG NO.: X-XZ7RV-M2F-XXXX-M2F-ZZ
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE: N/A
			PAGE: 1/1
			REVISION: A0

1

2

3

4