

RoHS

Specifications(规格):


- 1.Impedance(特性阻抗): 50Ω;
- 2.Frequency (工作频率): DC~6GHz;
- 3.VSWR (电压驻波比): 1.50@3GHz; 1.60@6GHz; .
- 4.Insulation resistance(绝缘阻抗): $\geq 100\text{M}\Omega$;
- 5.Dielectric withstand voltage (介质耐电压): 800V AC;
- 6.Mating cycles (耐久性): ≥ 25 cycles;
- 7.Retention force latch(保持力): $\geq 110\text{N}$;
- 8.Temperature range(使用温度): $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$;

PART NO.:

X Z X R 2 - M4M-XXXX-K1M- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302
8: RG174LL

- ② Successive number: 1~Z
③ Length (mm): 1000=1000mm
④ Coding A: A~Z
⑤ Coding B (B1~B4): A~Z



接点表(Wiring Table)

A端(A port)	Cable	B端(B port)
A1 [Pin shell]	Conductor Braid	Pin Shell] B1
A2 [Pin shell]	Conductor Braid	Pin Shell] B2
A3 [Pin shell]	Conductor Braid	Pin Shell] B3
A4 [Pin shell]	Conductor Braid	Pin Shell] B4

4-Length

①

LABEL

②

④

③ x4

B4

B1

B端

B2

B3

PART NO.		Length (mm/inch)	TOLERANCES (mm/inch)
XZ8R2-M4M-500-K1M-ZZ		500 [19.685]	± 10 [0.394]
XZ8R2-M4M-1000-K1M-ZZ		1000 [39.370]	± 15 [0.591]
XZ8R2-M4M-1500-K1M-ZZ		1500 [59.055]	± 15 [0.591]
XZ8R2-M4M-2000-K1M-ZZ		2000 [78.740]	± 20 [0.787]
XZ8R2-M4M-3000-K1M-ZZ		3000 [118.110]	± 30 [1.181]
DESIGN	希文	VIEW:	MODEL TYPE: Assembly cable, MINI FAKRA series
CHECKED		UNIT: mm/in	PART NO.: XZ8R2-M4M-XXXX-K1M-ZZ
APPROVED		SIZE: A4	DWG NO.: X-XZ8R2-M4M-XXXX-K1M-ZZ
SCALE			PAGE
N/A			1/1
REVISION			A0

4	Clip	Connector Clip: CC20SFT712	1PC	
3	Connector	FAKRA Male connector,Z Code	4SET	
2	Connector	MINI FAKRA Male connector(R),Z Code	1SET	
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃	4PCS	
NO.	NAME	SPEC.	Q'TY	NOTE
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn				

XKB 星坤
Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED