

RoHS

Specifications(规格):

- 1.Impedance(特性阻抗): 50Ω;
- 2.Frequency (工作频率): DC~6GHz;
- 3.VSWR (电压驻波比): 1.60 Max.
- 4.Insulation resistance(绝缘阻抗): $\geq 100M\Omega$;
- 5.Dielectric withstand voltage (介质耐电压): 800V AC;
- 6.Mating cycles (耐久性): ≥ 25 cycles;
- 7.Retention force latch(保持力): $\geq 110N$;
- 8.Temperature range(使用温度): $-40^{\circ}C \sim +105^{\circ}C$;

PART NO.:

X Z X R V - M2F-XXXX-K1M- X X
① ② ③ ④ ⑤

① Cable TYPE:


- 3: RG174
4: 1.5DS
7: Dacar302/RTK031
8: RG174LL

② Successive number: 1~Z


③ Length (mm): 1000=1000mm

④ Coding A: A~Z

⑤ Coding B: A~Z



接点表(Wiring Table)



PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ7RV-M2F-500-K1M-ZZ	500 [19.685]	± 10 [0.394]
XZ7RV-M2F-1000-K1M-ZZ	1000 [39.370]	± 15 [0.591]
XZ7RV-M2F-2000-K1M-ZZ	2000 [78.740]	± 20 [0.787]
XZ7RV-M2F-3000-K1M-ZZ	3000 [118.110]	± 30 [1.181]
XZ7RV-M2F-4000-K1M-ZZ	4000 [157.480]	± 60 [2.362]

3	Connector	FAKRA Male connector,Z Code	2SET	
2	Connector	Vertical Double MINI FAKRA Female Connector,Z Code	1SET	R版
1	Cable	RTK031 Cable PVC OD3.30 Black,-40~105℃	2PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB 星坤
Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希文	VIEW:	MODEL TYPE: Assembly cable, Vertical,Double MINI FAKRA series
CHECKED		UNIT: mm/in	PART NO.: XZ7RV-M2F-XXXX-K1M-ZZ
APPROVED		SIZE: A4	DWG NO.: X-XZ7RV-M2F-XXXX-K1M-ZZ
			SCALE PAGE REVISION N/A 1/1 A0