

1

2

3

4


RoHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.10.28	

PART NO.:

X Z X R 1 - M4F-XXXX-K1F- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302
8: RG174LL
- ② Successive number: 1~Z
- ③ Length (mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B (B1~B4): A~Z




接点表(Wiring Table)

A端(A port)	Cable	B端(B port)
A1 [Pin shell]	Conductor Braid	Pin Shell B1
A2 [Pin shell]	Conductor Braid	Pin Shell B2
A3 [Pin shell]	Conductor Braid	Pin Shell B3
A4 [Pin shell]	Conductor Braid	Pin Shell B4

PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ8R1-M4F-500-K1F-ZZ	500 [19.685]	±10 [0.394]
XZ8R1-M4F-1000-K1F-ZZ	1000 [39.370]	±15 [0.591]
XZ8R1-M4F-1500-K1F-ZZ	1500 [59.055]	±15 [0.591]
XZ8R1-M4F-2000-K1F-ZZ	2000 [78.740]	±20 [0.787]
XZ8R1-M4F-3000-K1F-ZZ	3000 [118.110]	±30 [1.181]

3	Connector	FAKRA Female connector,Z Code	4SET	
2	Connector	MINI FAKRA female connector(R),Z Code	1SET	
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃	4PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

	DESIGN	希文	VIEW: 	MODEL TYPE: Assembly cable, MINI FAKRA series		
	CHECKED		UNIT: mm/in	PART NO.: XZ8R1-M4F-XXXX-K1F-ZZ		
	APPROVED		SIZE: A4	DWG NO.: X-XZ8R1-M4F-XXXX-K1F-ZZ		
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/1	REVISION A0

1

2

3

4