

RoHS


Specifications(规格):

- 1.Impedance(特性阻抗) : 50Ω;
2.Frequency (工作频率) : DC~6GHz;
3.VSWR (电压驻波比) : 1.50@3GHz; 1.60@6GHz; .
4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
5.Dielectric withstand voltage (介质耐电压) : 800V AC;
6.Mating cycles (耐久性) : ≥25 cycles;
7.Retention force latch(保持力) : ≥110N;
8.Temperature range(使用温度): -40℃~+105℃;


PART NO.:

X Z X T X - M4F-XXXX-M4F- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302
8: RG174LL
② Successive number: 1~Z
③ Length (mm): 1000=1000mm
④ Coding A: A~Z
⑤ Coding B (B1~B4): A~Z




接点表(Wiring Table)



PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ7T1-M4F-1000-M4F-ZZ	1000 [39.370]	±15 [0.591]
XZ7T1-M4F-1500-M4F-ZZ	1500 [59.055]	±15 [0.591]
XZ7T1-M4F-2000-M4F-ZZ	2000 [78.740]	±20 [0.787]
XZ7T1-M4F-3000-M4F-ZZ	3000 [118.110]	±30 [1.181]
XZ7T1-M4F-4000-M4F-ZZ	4000 [157.480]	±60 [2.362]

2	Connector	MINI FAKRA female connector(T),Z Code	2SET	
1	Cable	RTK031 Cable PVC OD3.30 Black,-40~105℃	4PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

	DESIGN	希文	VIEW: 	MODEL TYPE: Assembly cable, MINI FAKRA series		
	CHECKED		UNIT: mm/in	PART NO.: XZ7T1-M4F-XXXX-M4F-ZZ		
	APPROVED		SIZE: A4	DWG NO.: X-XZ7T1-M4F-XXXX-M4F-ZZ		
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/1	REVISION A0