



P.C.B Layout

浙江博穆精密电子有限公司

图名:

2.0-2xNA

图号:

XXXXXXXXXXXXXXXXXXXX

未标注公差

XX.  $\pm 0.40$

XX.°  $\pm 2^\circ$

X.  $\pm 0.30$

.XX°  $\pm 1^\circ$

.X  $\pm 0.20$

.XX  $\pm 0.15$

绘制:

韩金锋

单位: MM

签发:

比例: 1:1

审核:

视图:

## 一. 电气性能:

1-1. 额定电流: 3A AC DC.

1-2. 接触电阻:  $\leq 20\text{m}\Omega$

1-3. 绝缘电阻:  $\geq 1000\text{M}\Omega$

1-4. 耐压: 550V AC/Minute

## 二. 物理特性:

2-1. 操作温度:  $-55^\circ\text{C} \sim 105^\circ\text{C}$

2-2. 焊接温度:  $+250^\circ\text{C}$ , 10s max

## 三. 材质:

3-1. 塑胶: 6T (Black) UL94V-0

3-2. 插针: Brass/Gold plated

注意:  $3 \leq n \leq 32$  的自然数