

1

2

3

4

RoHS


REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.10.28	

PART NO.:

X Z X R X - M4F-XXXX-K1M- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302
8: RG174LL
- ② Successive number: 1~Z
- ③ Length (mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B (B1~B4): A~Z



接点表(Wiring Table)

A端(A port)	Cable	B端(B port)
A1 [Pin shell]	Conductor Braid	Pin Shell B1
A2 [Pin shell]	Conductor Braid	Pin Shell B2
A3 [Pin shell]	Conductor Braid	Pin Shell B3
A4 [Pin shell]	Conductor Braid	Pin Shell B4

PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ7R1-M4F-500-K1M-ZZ	500 [19.685]	±10 [0.394]
XZ7R1-M4F-1000-K1M-ZZ	1000 [39.370]	±15 [0.591]
XZ7R1-M4F-2000-K1M-ZZ	2000 [78.740]	±20 [0.787]
XZ7R1-M4F-3000-K1M-ZZ	3000 [118.110]	±30 [1.181]
XZ7R1-M4F-4000-K1M-ZZ	4000 [157.480]	±60 [2.362]

3	Connector	FAKRA Male connector,Z Code	4SET	
2	Connector	MINI FAKRA Female connector(R),Z Code	1SET	
1	Cable	RTK031 Cable PVC OD3.30 Black, -40~105℃	4PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

DESIGN 希文

CHECKED

APPROVED

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:
Assembly cable, MINI FAKRA series

PART NO.:
XZ7R4-M4F-XXXX-K1M-ZZ

DWG NO.:
X-XZ7R4-M4F-XXXX-K1M-ZZ

SCALE N/A

PAGE 1/1

REVISION A0

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4