











MATERIAL
HOUSING : THERMO PLASTIC UL94V-0 BLACK
CONTACT : COPPER ALLOY
PEG : COPPER ALLOY
SPECIFICATION
CURRENT RATING : 0.5A 50V AC/DC
CONTACT RESISTANCE : 55 mΩ MAX
INSULATION RESISTANCE : 500 MΩ MIN AT 500V DC
OPERATING TEMPERATURE : -55°C~80°C

LP08A6-*52-BOR
PACKING: R:REEL
O:STANDARD SPECIFICATIONS
COLOR:BLACK
PIN
PLATING TYPE G:1u" Au Min(GOLD FLASH)
3:3u" Au Min F:10u" Au Min
HEIGHT:A6--10.6H
0.80 PITCH
LXWCONN MINI PCI CONNECTOR SERIES



-D- IS THE TOP SURFACE OF PCB.
RECOMMENDED P.C.BOARD PATTERN LAYOUT

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS(SHENZHEN)CO., LTD

一般公差 GENERAL TOLERANCE .X ±0.35 .XX ±0.25 .XXX ±0.10 ANGLES ±1°	制图 (DR): Jerry 2020.02.21	品名(TITLE): 0.80MM PITCH MINI PCI EXPRESS H=10.6mm CONNECTOR
审核 (CHD):	料号(PART NO): LP08A6-*52-BOR	
版本 (REV) A	比例(SCALE) 1:1	单位(UNITS) mm
核准 (APPD): Tong 2020.02.21	张数(SHEET) 1 OF 1	图幅(SIZE) A4

RoHS Compliant 2013/95/EC

修订 (REV)	修改摘要 (REVISION DESCRIPTION)	签名 (SIGNATURE)	日期 (DATE)
SER			