








Recommended PC board pattern
(TOP VIEW)




Dimension table(mm)

No. of pins	A	B	C	D	E	F
12	7.40	4.00	6.30	6.30	4.00	0.10
14	8.20	4.80	7.10	7.10	4.80	
16	9.00	5.60	7.90	7.90	5.60	
20	10.60	7.20	9.50	9.50	7.20	
22	11.40	8.00	10.30	10.30	8.00	
24	12.20	8.80	11.10	11.10	8.80	
26	13.00	9.60	11.90	11.90	9.60	
30	14.60	11.20	13.50	13.50	11.20	
34	16.20	12.80	15.10	15.10	12.80	
40	18.60	15.20	17.50	17.50	15.20	
50	22.60	19.20	21.50	21.50	19.20	0.15
60	26.60	23.20	25.50	25.50	23.20	
64	28.20	24.80	27.10	27.10	24.80	
80	34.60	31.20	33.50	33.50	31.20	
100	42.60	39.20	41.50	41.50	39.20	
120	50.60	47.20	49.50	49.50	47.20	
140	58.60	55.20	57.50	57.50	55.20	

- ELECTRICAL REQUIREMENTS
RATED VOLTAGE: 60V AC/DC
RATED CURRENT: 0.5 AMPS
CONTACT RESISTANCE: 60 MΩ MAX.
INSULATION RESISTANCE: INITIAL VALUE OF 1000 MΩ MIN
INSULATION VOLTAGE: 250V AC FOR 1 MINUTE
- MECHANICAL PERFORMANCE REQUIREMENTS
INSERTION FORCE: MAXIMUM 57.46N.
OUTPUT: MINIMUM 8.50N
- ENVIRONMENTAL REQUIREMENTS
OPERATING TEMPERATURE: -55 °C ~+85 °C
- MATERIALS:
CONTACT: PHOSPHOR BRONZE
HOUSING: HIGH TEMPERATURE UL 94-V0

LB 3 22-G XX S-W 0 R 01
 RUNNING NUMBER
 PACKING: R:REEL
 0:MYLAR
 COLOR:CREAM COLORED
 SOCKET
 PIN:
 PLATING: GOLD FLASH
 FEMALE HEIGHT:2.2mm
 0.8 BTB
 LXWCONN BTB CONNECTOR SERIES



LXW 连兴旺电子(深圳)有限公司
 connectivity LXWCONN ELECTRONICS(SHENZHEN) CO., LTD

一般公差 GENERAL TOLERANCE .X ±0.35 .XX ±0.25 .XXX ±0.10 ANGLES ±1°		制图 (DR): Jerry 2020.03.21	品名(TITLE): AXN340 ASSEMBLY DRAWING			
审核 (CHKD):		料号(PART NO): LB322-GXXS-W0R01		比例(SCALE): 1:1		
批准 (APPD): Tong 2020.03.21		单位(UNITS): mm	张数(SHEET): 1 OF 1	图幅(SIZE): A4		