



SECTION **B-B**

HOUSING : THERMO PLASTIC UL94V-0 BLACK

CONTACT : COPPER ALLOY

PEG : COPPER ALLOY



SPECIFICATION

CURRENT RATING : 0.5A 50V AC/DC

CONTACT RESISTANCE : 55 mΩ MAX

INSULATION RESISTANCE : 500 MΩ MIN AT 500V DC

OPERATING TEMPERATURE : -55°C~80°C



RECOMMENDED P.C.BOARD PATTERN LAYOUT



一般公差	
GENERAL TOLERANCE	
.X	±0.35
.XX	±0.25
.XXX	±0.10
ANGLES	+1°

制图 (DR):	Jerry 2020.03.21
----------	---------------------

品名(TITLE):	0.80MM PITCH MINI PCI EXPRESS H=9.9mm CONNECTOR
------------	--

审核 (CHKD):

Tong

比例(SCALE)

	單位 (UNITS)
--	------------

张数(SHEET)

图幅 (SIZE)	
-----------	--

核准 (APPD): 2020.03.21

1:1

mm

1 OF 1

A4

