






RFCOMMENDD P.C.BOARD LAYOUT



Specifications
 Current Rating:0.5Amp
 Insulation Resistance:500MΩMin.
 Dielectric Withstanding Voltage:200VA
 Contact Resistance:30mΩMax.
 Operating Temperature:−40°C to +105°C
 Materials
 Contact Material:Phosphor Bronze
 Insulator Material:LCP High Temperature
 Thermoplastic, UL 94V-0

合高	H	H1
4.00H	2.80	1.80
4.50H	3.30	1.80
5.00H	3.80	1.80
5.50H	4.30	2.30
6.00H	4.80	2.30
6.50H	5.30	2.30
7.00H		

LB3** - G**P - WOR

PACKING: R:REEL
 O:STANDARD SPECIFICATIONS
 COLOR:WHITE
 P: PLUG
 PIN
 PLATING: G:GOLD FLASH/B:FOG TIN
 HEIGHT:28-2.8H, 33-3.3H, 38-3.8H,
 43-4.3H, 48-4.8H, 53-5.3H,
 3.0.8 BTB
 LXWCONN BTB CONNECTOR SERIES




Circuits	Dimensions(mm)				
	排列	A	B	C	D
6	2*3	4.30	2.80	1.60	3.40
8	2*4	5.10	3.60	2.40	4.20
10	2*5	5.90	4.40	3.20	5.00
12	2*6	6.70	5.20	4.00	5.80
14	2*7	7.50	6.00	4.80	6.60
16	2*8	8.30	6.80	5.60	7.40
18	2*9	9.10	7.60	6.40	8.20
20	2*10	9.90	8.40	7.20	9.00
30	2*15	13.90	12.40	11.20	13.00
40	2*20	17.90	16.40	15.20	17.00
50	2*25	21.90	20.40	19.20	21.00

LXW 连兴旺电子(深圳)有限公司
 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

制图 (DR): Jerry 2020.03.21
 品名(TITLE): 0.80mm BTB PLUG
 审核 (CHKD): Tong 2020.03.21
 料号(PART NO): LB3**-G**P-WOR
 比例(SCALE): 1:1
 单位(UNITS): mm
 张数(SHEET): 1 OF 1
 图幅(SIZE): A4

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差
 GENERAL TOLERANCE:
 .X ±0.35
 .XX ±0.25
 .XXX ±0.10
 ANGLES ±1°



RoHS
 Compliant
 2013/05/EC