











Remark:
Rated current: 0.5 amperes
Contact resistance: 30 MΩ MAX.
Voltage resistance: 500V AC
Operating temperature: -40℃~+85℃
Metal materials: copper alloy
Housing: high temperature UL 94-v0



RECOMMENDED PCB LAYOUT(TOP VIEW)



PACKING: R:REEL/B:Blister box
O:STANDARD SPECIFICATIONS
COLOR:BLACK / WHITE
S: SOCKET

PLATING: G:GOLD FLASH

HEIGHTA3--10.3H

6:2.0 BTB

LXWCONN BTB CONNECTOR SERIES

Circuits	Dimensions(mm)				
	排列	A	B	C	D
20	2*10	23.90	18.00	22.10	22.40
22	2*11	25.90	20.00	24.10	24.40
24	2*12	27.90	22.00	26.10	26.40
26	2*13	29.90	24.00	28.10	28.40
28	2*14	31.90	26.00	30.10	30.40
30	2*15	33.90	28.00	32.10	32.40
32	2*16	35.90	30.00	34.10	34.40
36	2*18	39.90	34.00	38.10	38.40
40	2*20	43.90	38.00	42.10	42.40
50	2*25	53.90	48.00	52.10	52.40

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差 GENERAL TOLERANCE
.X ±0.35
.XX ±0.25
.XXX ±0.10
ANGLES ±1°

LXW 连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD	
制图 (DR): Jerry 2020.03.30	品名(TITLE): 2.0MM BTB母座 合高14.6mm
审核 (CHKD):	料号(PART NO): LB6A3-GXXS-B0R
版本 (REV): A	比例(SCALE): 1:1
核准 (APPD): Tong 2020.03.30	单位(UNITS): mm
	张数(SHEET): 1 OF 1
	图幅(SIZE): A4

RoHS
Compliant
2013/95/EC

