



1 2 3 4 5 6 7 8


A





B



C



D



L B 3 * * - G * * S - W O R

PLATING: G:GOLD FLASH/B:FOG TIN
HEIGHT:29-2.9H, 34-3.4H, 39-3.9H
3.0.8 BTB
BTB CONNECTOR SERIES

PACKING: R:REEL
O:STANDARD SPECIFICATIONS
COLOR:WHITE
S: SOCKET
PIN

Specifications
Current Rating:0.5Amp
Insulation Resistance:500MΩMin.
Dielectric Withstanding Voltage:200VA
Contact Resistance:30mΩMax.
Operating Temperature:-40°C to +105°C
Materials
Contact Material:Phosphor Bronze
Insulator Material:LCP High Temperature
Thermoplastic, UL 94V-0

合高	H
4.00H	2.90
4.50H	
5.00H	
5.50H	
6.00H	3.40
6.50H	
7.00H	3.90

Circuits	Dimensions(mm)				
	排列	A	B	C	D
6	2*3	4.30	2.80	1.60	3.40
8	2*4	5.10	3.60	2.40	4.20
10	2*5	5.90	4.40	3.20	5.00
12	2*6	6.70	5.20	4.00	5.80
14	2*7	7.50	6.00	4.80	6.60
16	2*8	8.30	6.80	5.60	7.40
18	2*9	9.10	7.60	6.40	8.20
20	2*10	9.90	8.40	7.20	9.00
30	2*15	13.90	12.40	11.20	13.00
40	2*20	17.90	16.40	15.20	17.00
50	2*25	21.90	20.40	19.20	21.00

慈溪市慈惠电子元件厂

一般公差 GENERAL TOLERANCE I: ±0.25 II: ±0.25 III: ±0.10 ANGLES: ±1°	Jerry 2020.03.21	品名(TITLE): 0.80mm BTB SOCKET
审核(Check):	料号(PART NO): LB3**-G**S-WOR	
版本(Rev): A	比例(SCALE): 1:1	单位(UNITS): mm
核准(APPD): Tong 2020.03.21	张数(SHEET): 1 OF 1	图幅(SIZE): A4

RoHS
Compliant
2013/5/ECPb
Free

1

2

3

4

5

6

7

8