





红色对插标识点
Red Insertion Marker



面板开孔尺寸
Panel cut-out size



产品材质及表面处理Product material and surface treatment
外壳enclosure: 黄铜镀铬 (Brass chrome plated)
内套Inner sleeve: 黄铜镀镍 (Brass nickel plated)
导体conductor: 黄铜镀金 (Brass gilded)
绝缘体insulator:PPS

产品性能Product performance
防护等级 (Ingress protection): 插合时IP68
若电缆外形足够圆, 并且组装过程保证密封良好, 那么可以达到IP68防护等级
插拔测试 (Plugging and unplugging test) >3000次
插合端针直径 (Mating pin diameter): (Φ0.9) / (Φ2.3)
测试电压 (Test Voltage): 875V
工作电压 (Operating Voltage): 400V
Φ0.9导体额定电流 (Rated current of Φ0.9 conductor): 3A
Φ2.3导体额定电流 (Rated current of Φ2.3 conductor): 25A
产品耐温 (The product is temperature resistant): -55° C / +150° C
盐雾腐蚀 (Salt Spray Corrosion): >72 hr
屏蔽性能 (Shielding performance): >75 dB (<10MHz) >40 dB (<1GHz)
抗振动 (Vibration-resistant): 10-2000Hz, 15g
抗冲击 (Impact-resistant): 100g, 6ms

G8	2F	1	04	1C	C	S	R	Y	T1
类型	系列	导体类型	导体数量	键位	外壳材质及电镀	绝缘体材质	定位点颜色	灌胶	上下平位
type	series	Conductor type	Number of conductors	Keys	Housing material and plating	Insulator material	Anchor point color	Potting	Upper and lower positions

未标注公差 Tolerances are not indicated 0~5: ±0.1 6~10: ±0.15 11~50: ±0.2 51~100: ±0.25 100+: ±25%	视图 view	 Dongguan Tongrui Electronic Technology Co., Ltd 东莞市通瑞电子科技有限公司			
	设计 DESIGNED				
	校对 CHECKED	型号 MODEL	G8. 2F. 104. 1C. CSRY. T1	单位 UNIT	mm
	审核 APPROVED	名称 PARTNAME	G8板后安装前固定插座 (焊接)	版本 REV	A/0
比例 SCALE	1:1	日期 date			

www.cntfre.com