








Remark:
 Rated current: 0.5 amperes
 Contact resistance: 30 MΩ MAX.
 Voltage resistance: 500V AC
 Operating temperature: -40℃~+85℃
 Metal materials: copper alloy
 Housing: high temperature UL 94-v0



RECOMMENDED PCB LAYOUT(TOP VIEW)



Circuits	Dimensions(mm)				
	排列	A	B	C	D
20	2*10	23.80	18.00	22.15	22.40
22	2*11	25.80	20.00	24.15	24.40
24	2*12	27.80	22.00	26.15	26.40
26	2*13	29.80	24.00	28.15	28.40
28	2*14	31.80	26.00	30.15	30.40
30	2*15	33.80	28.00	32.15	32.40
32	2*16	35.80	30.00	34.15	34.40
36	2*18	39.80	34.00	38.15	38.40
40	2*20	43.80	38.00	42.15	42.40
50	2*25	53.80	48.00	52.15	52.40

修订	修改摘要	签名	日期	版本
SER	REVISION DESCRIPTION	SIGNATURE	DATE	(REV)

一般公差
GENERAL TOLERANCE
.X ±0.35
.XX ±0.25
.XXX ±0.10
ANGLES ±1°

连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD				
制图 (DR):	Jerry	品名(TITLE):	2.0mm 直插BTB PLUG	
审核 (CHKD):		料号(PART NO):	LB682-XXXP-B0R	
核准 (APPD):	Tong	比例(SCALE):	单位(UNITS):	张数(SHEET):
	2020.03.30	1:1	mm	1 OF 1
				图幅(SIZE): A4