





- 说明:
- 1. 胶芯 :LCP 黑色 ;UL94V-0.
 - 2. 端子:C2680 T=0.15mm, 半金镍 G/F" (功能区)
 - 3. 外壳 :C2680 T=0.25mm, 镀雾锡
 - 4. 额定电流 :2A 最大.
 - 5. 耐电压 :100V(AC)/1 分钟至少.
 - 6. 接触阻抗 :30mΩ 最大.
 - 7. 绝缘阻抗 :100MΩ 最小.
 - 8. 插入力 :3.57Kgf 最大.
 - 9. 拔出力 :1.0Kgf 初始 最小 ; 测试后 0.81Kgf 最小
 - 10. 温度范围 : -30° C~+80° C

GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. HMT-MICRO USB B	TITLE: MIRCO USB 5S 4.85 牛角插座		
.XX ±0.20	X.X* ±1°				
.XXX ±0.10	X.XX* ±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1



说明：

- 1. 将检查合格的产品，放入承载带中，一盘包装 1000/1500PCS
- 2. 将 15 盘承载带放入纸箱中：
- 3. 将纸箱封装好，贴上标签。

每箱数量	净重 (Kg)	毛重 (Kg)
15000/22500PCS	xxx	xxx

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO.	TITLE:	
.XX ±0.20	X.X° ±1°	HMT-MICRO USB B	MIRCO USB 5S 4.85 牛角插接处	
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		MM
				SHEET
				N:A 1/1