








RoHs



A-A




PCB.WELDING DRAWING (TOLERANCE:±0.05)



VER	MARK	PR. BY	DESCRIPTION	DATE

Technical requirements	
Characteristic impedance	50 Ω
Frequency range	0-6GHz
Contact resistance	
Inner conductor	≤3m Ω
Outer conductor	≤2m Ω
Insulated resistance	≥5000M Ω
Salt spray time	48H
Separation force	≥0.28N
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	

1	半螺铜座	1	黄铜	镀金
2	尖头母针	1	黄铜	镀金
3	绝缘体	1	PTFE	
序号	名称	数量	材料	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 HMT CONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO.	TITLE:		
.XX ±0.20	X.X° ±1°	HMT-SMA-KE-Z347A	SMA 内孔 正牌		
.XXX ±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1