





1-1. CONTACT: AU 1U" PLATING ON CONTACT AREA,
100~200U" SN PLATING ON SOLDER TAILS,
50U" NICKEL UNDERPLATING VOER ALL;

2. *PRODUCT SPECIFICATIONS:*







2-1. VOLTAGE RATING: 100V

2-2. CURRENT RATING: 0.5A

2-3. INSULATION RESISTANCE: 1000 MEG. OHM MIN

2-4. CONTACT RESISTANCE: 100 MILL. OHM MAX

2-5. OPERATION TEMPERATURE: -20° TO $+85^{\circ}$



PAD AREA

KEEP OUT AREA

RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ± 0.05

TF CARD PIN DEFINE			
PIN NO.	NAME	TYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)

GENERAL TOLERANCES
UNLESS SPECIFIED



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

.X	± 0.35
----	------------

5	$X^\circ \pm 3^\circ$
---	-----------------------

5	$XX^\circ + 2^\circ$
---	----------------------

[illegible]

PART NO.

HMT-TF-1307

DESIGN: *James*

CLER	Talca
------	-------

MANUFACTURE DWG

TITLE:

1.6 掀盖T卡



CUSTOMER

SIZE	UNITS
------	-------





SCALE	SHEET
-------	-------

RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE




1、产品平整包装入载带




天地板

3、11 盘整齐叠放，上下各加一块天地板。



4、装箱



NOTE:

1. QUANTITY/1500 PCS

数量/卷:1500PCS

2. QUANTITY/INNER CARTON:1500X11=16500PCS

数量/箱:1500X10=15000PCS

3. FREE 25 CAVES THE FRONT CARRIER AND FREE

25 CAVES IN THE END CARRIER

包装带内圈空25格，外圈空25格

GENERAL TOLERANCES
UNLESS SPECIFIED

.X ±0.35 .X° ±3°

.XX ±0.25 .XX° ±2°

.XXX ±0.15

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-TF-1307

TITLE:
T-FLASH CARD HINGED
H1.6 掀盖T卡

DESIGN: James

CHED: Talen

APPD: Sophia

CUSTOMER

SIZE

SCALE

UNITS

MM

SHEET

N:A 1/1