




一、 MATERIAL:

- 1. Insulator:PBT+30%Glass Fiber
- 2. Contact:Brass
- 3. Contact Plated: Glod Plated
- 4. Shell:Steel,Nickel Plated

二、 SPECIFICATION:

- 1. Current Rating:3 AMPS
- 2. Insulation Resistance: 100MΩ MIN. At 500VDC
- 3. Dielectric Strength: 500V for One minute
- 4. Operation Temperature: -55° C~+105° C.

* 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ±0.05

GENERAL TOLERANCES UNLESS SPECIFIED				HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X	±0.30	X.°	±5°	PART NO.	TITLE:		
.XX	±0.20	X.X°	±1°	DSUB-DS1037-09FN	DR9F 叉锁		
.XXX	±0.10	X.XX°	±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG				CHED: Talen		A4	MM
				APPD: Sophia		SCALE	SHEET
						N:A	1/1